

WORKSHOP[®] MD

WET/DRY VACS

4.25

PEAK HP

6

US
GALLON

- **Stainless Steel Drum Cleans Up Easily For A Professional Appearance**
- **Qwik Lock[®] Filter Fastening System For Easy Filter Changes**
- **On-Board Storage Keeps Accessories Secure And Within Close Reach**
- **Integral Blowing Port For Added Versatility**
- **Quick-Release Locking Hose Stays Secure During Use**
- **Large Carry Handle For Easy Transport**

STAINLESS STEEL PORTABLE VAC

With 360° maneuverability this sharp looking 6 Gallon Stainless Steel Vac is compact and easy to carry, transport and store.



1 7/8"

DIAMETER



Includes: Vac, Hose, Utility Nozzle, Wet Nozzle, 2 Extension Wands, Qwik Lock[®] Filter, Owner's Manual

WS0600SS

5 YEAR*
LIMITED
WARRANTY

WORKSHOP[®] MD

WET/DRY VACS

www.WORKSHOPvacs.com

4.25

PEAK HP

6

US
GALLON

SPECIFICATIONS

Drum Size	6 Gal / 22 L
Peak H.P.	4.25
Voltage	120
Amps	8.3
CFM	68.7
Static Lift	63.3 in
Max Air Watts	177
Blowing Capability	Yes
Cord Length	10' / 3 m
Hose Length	7' / 2,1 m
Drain Port	No
Construction	Stainless Steel
Accessory Size	1 7/8" / 4,8 cm
Accessory Storage	Yes - Caster Feet
U.L. Listed	Yes

10' / 3M



OPTIONAL FILTRATION

Fine Dust Filter	WS22200F
HEPA Media Filter	WS23200F
Wet Application Filter	WS24200F



Qwik Lock[®] Filter Fastening System –
Makes installing or removing your filter
quick, easy and secure.



WORKSHOP[®] Wet/Dry Vacs
8100 West Florissant
St. Louis, MO 63136

1-888-455-8724



WORKSHOPbrand

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.