

WORKSHOP[®] MD

WET/DRY VACS

3.5
PEAK HP

6
US
GALLON

- On-Board Storage Keeps Accessories Secure And Within Close Reach
- Qwik Lock[®] Filter Fastening System For Easy Filter Changes
- Integral Blowing Port For Added Versatility
- Quick-Release Locking Hose Stays Secure During Use
- Large Carry Handle For Easy Transport

GENERAL PURPOSE VAC

With 360° swivel caster mobility and on-board accessory storage, the 6 Gallon Vac is handy for all sorts of garage and shop messes.



1 7/8"

DIAMETER



Includes: Vac, Hose, Utility Nozzle, 2 Extension Wands, Standard Filter, Dust Bag, Owner's Manual

WSO610VA

5 YEAR*
LIMITED
WARRANTY

WORKSHOP[®] MD

WET/DRY VACS

www.WORKSHOPvacs.com

3.5

PEAK HP

6

US
GALLON

SPECIFICATIONS

Drum Size	6 Gal /22 L
Peak H.P	3.5
Voltage	120
Amps	7.8
CFM	66
Static Lift	65 in
Max Air Watts	188
Blowing Capability	Yes
Cord Length	10' / 3 m
Hose Length	7' / 2,1 m
Drain Port	No
Construction	Polypropylene
Accessory Size	1 7/8" / 4,8 cm
Accessory Storage	Yes- Caster feet
U.L. Listed	Yes
Standard Filter	WS21200F
Dust Collection Bag	WS32090F

10'/3M

Top carrying handle provides easy transport.

1 7/8" x 7' Quick-release locking hose stays secure during use.



Blowing port for added versatility.

Accessory storage on caster feet keep accessories close at hand.

Tough, copolymer drum resists dents and cracks, will not rust.



Qwik Lock[®] Filter Fastening System –
Makes installing or removing your filter
quick, easy and secure.



WORKSHOP[®] Wet/Dry Vacs
8100 West Florissant
St. Louis, MO 63136

1-888-455-8724



WORKSHOPbrand

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.