

WORKSHOP[®] MD

WET/DRY VACS

5.0

PEAK HP

12

US
GALLON

- On-Board Storage Keeps Hose And Accessories Secure And Within Reach
- Qwik Lock[®] Filter Fastening System For Easy Filter Changes
- Dual-Flex[®] Locking Hose Offers 180° Flexibility At Both Hose Ends For Better Maneuverability
- Large Drain For Easier Liquid Disposal
- Large Carry Handle For Easy Transport
- Integral Blowing Port For Added Versatility

HIGH-POWER GENERAL PURPOSE VAC

Equally at home on the job or in the shop, the 12 Gallon General Purpose Vac delivers the ideal combination of performance, drum capacity and convenience.



2 1/2"

DIAMETER



Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Wet Nozzle, 2 Extension Wands, Locking Sleeve, Filter, Dust Bag, Owner's Manual

WSI200VA

5 YEAR*
LIMITED
WARRANTY

WORKSHOP[®] MD

WET/DRY VACS

www.WORKSHOPvacs.com

5.0

PEAK HP

12

US
GALLON

SPECIFICATIONS

Drum Size	12 Gal / 45 L
Peak H.P.	5.0
Voltage	120
Amps	10.0
CFM	135
Static Lift	47 in
Max Air Watts	209
Blowing Capability	Yes
Cord Length	15' / 4,5 m
Hose Length	7' / 2,1 m
Drain Port	Yes
Construction	Polypropylene
Accessory Size	2 1/2" / 6,4 cm
Accessory Storage	Yes - Caster Feet
U.L. Listed	Yes
Standard Filter	WS21200F
Dust Collection Bag	WS32200F

15' / 4,5 M



OPTIONAL FILTRATION

Fine Dust Filter	WS22200F
HEPA Media Filter	WS23200F
Wet Application Filter	WS24200F



Qwik Lock[®] Filter Fastening System –
Makes installing or removing your filter
quick, easy and secure.



WORKSHOP[®] Wet/Dry Vacs
8100 West Florissant
St. Louis, MO 63136

1-888-455-8724



WORKSHOPbrand

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.