

WORKSHOP[®] MD

WET/DRY VACS

2.5
PEAK HP

5
US
GALLON

- Casters Swivel 360° For Maximum Mobility
- Large Carry Handle For Easy Transport
- Quick-Release Locking Hose Stays Secure During Use
- Integral Blowing Port For Added Versatility

GENERAL PURPOSE VAC

With 360° swivel caster mobility and a large carry handle for easy transport, the 5 Gallon Vac is easy to transport to all sorts of garage and shop messes.



1 7/8"

DIAMETER



Includes: Vac, Hose, Utility Nozzle, 2 Extension Wands, Standard Filter Bag, Owner's Manual

WS0500VA

5 YEAR*
LIMITED
WARRANTY

WORKSHOP[®] MD

WET/DRY VACS

www.WORKSHOPvacs.com

2.5

PEAK HP

5

US
GALLON

SPECIFICATIONS

Drum Size	5 Gal / 18 L
Peak H.P.	2.5
Voltage	120
Amps	5.8
CFM	64
Static Lift	52 in
Max Air Watts	140
Blowing Capability	Yes
Cord Length	10' / 3 m
Hose Length	7' / 2,1 m
Drain Port	No
Construction	Polypropylene
Accessory Size	1 7/8" / 4,8 cm
Accessory Storage	No
U.L. Listed	Yes
Filter Bag	WS01025F

10'/3M

Top carrying handle provides easy transport.

Blowing port for added versatility.

1 7/8" x 7" Quick-release locking hose stays secure during use.

Casters swivel 360° for maximum mobility.

Tough, copolymer drum resists dents and cracks, will not rust.



OPTIONAL FILTRATION

Standard Filter	WS11045F
Fine Dust Filter	WS12045F



Qwik Lock[®] Filter Fastening System –
Makes installing or removing your filter quick, easy and secure.



WORKSHOP[®] Wet/Dry Vacs
8100 West Florissant
St. Louis, MO 63136

1-888-455-8724



WORKSHOPbrand

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.