

# WORKSHOP<sup>®</sup> MD

WET/DRY VACS



With over 45 years of Wet/Dry Vac engineering and manufacturing excellence under our belts, we produce quality vacs, accessories and filters for commercial users, construction professionals and do-it-yourselfers. WORKSHOP Wet/Dry Vacs deliver unmatched power, performance and durability and include thoughtful features that make our vacs easier and more convenient to use. Multiple filtration options, including HEPA\* Media, dust collection bags and our patent-pending Wet Filter help keep the environment free of harmful contaminants, vac components free from damage and make debris disposal more convenient. Our patented Qwik-Lock™ filter fastening system makes filter cleaning and replacement a breeze...no need for tools, caps or fasteners.

WORKSHOP innovation doesn't stop at the filter. The patent-pending Dual-Flex™ locking hose allows for 180° flexibility at both hose-ends, resists crimping and collapsing and remains securely attached to the vac during use yet detaches quickly and easily for storage. To make your clean-up time even faster and more trouble-free, try the new Roll Tight™ locking sleeve which makes loose wand and accessory connections a thing of the past.

Whether its a general purpose vac, a high-powered, portable vac, a Contractor Vac or our Mobile Vac Station, with WORKSHOP...your mess has met its match!

\*HEPA – High Efficiency Particulate Air



Because after all, isn't that what it's really all about? Whether you're cleaning up the job site mess, a flood from a leaky appliance, your dusty garage or a cluttered car, you need a WORKSHOP Wet/Dry Vac to get the job done quickly and efficiently.



\* 3 Year Limited on WS0250VA  
See Website for Details. [www.WORKSHOPvacs.com/Warranty](http://www.WORKSHOPvacs.com/Warranty)

Gallons indicated reflect drum volume, not necessarily collection capacity.  
Actual capacity dependent upon type of debris collected, condition of filter, and other factors.  
Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer.  
All specification data subject to change without notice.

**COMPACT VAC**
**WS0250VA**
**1.75**
**PEAK HP**
**2.5**
**US  
GALLON**
**1¼"**
**DIAMETER**

This compact, lightweight vac is so easy to carry and store, and really handy for quick pick-ups around the house.

Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Filter Bag


**PORTABLE VAC**
**WS0300VA**
**3.5**
**PEAK HP**
**3**
**US  
GALLON**
**1⅞"**
**DIAMETER**

With the power of our 9 Gallon vac, a unique built-in dust pan feature and unmatched portability, the 3 Gallon Portable Vac is the ideal vac for auto, job site and workbench cleaning.

Includes: Vac, Hose, Car Nozzle, Standard Filter, Dust Bag



**PORTABLE VAC****WSO400VA****5.0**

PEAK HP

**4**US  
GALLON**1 7/8"**

DIAMETER

With a bit more collection capacity and power, the 4 Gallon Portable Vac delivers high performance in a compact package and is convenient to carry, transport and store.

Includes: Vac, Hose, Car Nozzle, Muffler/Diffuser, Standard Filter, Dust Bag

**CONTRACTOR VAC****WSO450VA****5.0**

PEAK HP

**4.5**US  
GALLON**1 7/8"**

DIAMETER

The Contractor Vac is all about power, transportability and organized on-board storage. With hinged compartments to store the cord and all it's tools, this vac stacks and stores tidily in a truck or van.

Includes: Vac, Hose, Utility Nozzle, Crevice Tool, Dusting Brush, 2 Extension Wands, Fine Dust Filter, Dust Bag



## PORTABLE WALL MOUNT VAC

WSO500WM

**5.0**

PEAK HP

**5**

US  
GALLON

**1 7/8"**

DIAMETER

Mount it to the wall or take it with you, this vac helps save floor space while providing all the power and reach you need.

Includes: Vac, 2 Hoses, Utility Nozzle, Crevice Tool, Car Nozzle, Dusting Brush, 2 Extension Wands, Muffler/Diffuser, Standard Filter



## GENERAL PURPOSE VAC

WSO600VA

**2.5**

PEAK HP

**6**

US  
GALLON

**1 7/8"**

DIAMETER

With 360° swivel caster mobility and on-board accessory storage, the 6 Gallon General Purpose Vac is handy for all sorts of garage and shop messes.

Includes: Vac, Hose, Utility Nozzle, 2 Extension Wands, Standard Filter, Dust Bag



**GENERAL PURPOSE VAC****WS0900VA****3.5**

PEAK HP

**9**US  
GALLON**1 7/8"**

DIAMETER

Stepping up in power and drum capacity the 9 Gallon General Purpose Vac remains easy to maneuver and store.

Includes: Vac, Hose, Utility Nozzle, Wet Nozzle, 2 Extension Wands, Standard Filter, Dust Bag

**HIGH-POWER GENERAL PURPOSE VAC****WSI200VA****5.0**

PEAK HP

**12**US  
GALLON**2 1/2"**

DIAMETER

Equally at home on the job or in the shop, the 12 Gallon General Purpose Vac delivers the ideal combination of performance, drum capacity and convenience.

Includes: Vac, Hose, Utility Nozzle, 2 Extension Wands, Car Nozzle, Wet Nozzle, Standard Filter, Locking Sleeve, Dust Bag



## DETACHABLE BLOWER VAC

WSI200DE

**5.0**

PEAK HP

**12**

US  
GALLON

**2½"**

DIAMETER

Two tools in one, the power head of this 12 Gallon Vac easily converts to a powerful hand held blower for even more cleaning versatility.

Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Wet Nozzle, Blower Nozzle, Male-Male Adapter, 2 Extension Wands, Locking Sleeve, Standard Filter



## HIGH-POWER CART VAC

WSI400CA

**6.0**

PEAK HP

**14**

US  
GALLON

**2½"**

DIAMETER

Rough terrain mobility, reduced noise, high performance and rugged 2-piece drum construction are this vac's hallmarks.

Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Wet Nozzle, 2 Extension Wands, Locking Sleeve, Fine Dust Filter, Dust Bag





**HIGH-CAPACITY VAC****WSI600VA****6.5**

PEAK HP

**16**US  
GALLON**2½"**

DIAMETER

This no-nonsense 16 Gallon Vac has the power, durability and collection capacity to be the jobsite workhorse.

Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Wet Nozzle, 2 Extension Wands, Locking Sleeve, Standard Filter

**STAINLESS STEEL VAC****WSI600SS****6.5**

PEAK HP

**16**US  
GALLON**2½"**

DIAMETER

Featuring a Stainless Steel drum and rough terrain cart, this vac outperforms under the toughest of conditions.

Includes: Vac, Hose, Utility Nozzle, Crevice Tool, Car Nozzle, Wet Nozzle, 2 Extension Wands, Locking Sleeve, Fine Dust Filter, Dust Bag



## MOBILE VAC STATION

**WS1100CA**

**6.5**

PEAK HP

**11**


US  
GALLON

**1 7/8"**

DIAMETER

The Mobile Vac Station is the ultimate in organized storage, easy debris disposal, power and convenience.

Includes: Vac, Hose, Utility Nozzle, Crevice Tool, Dusting Brush, Wet Nozzle, Claw Nozzle, 2 Extension Wands, Fine Dust Filter



## AIR MOVER

**WS1625AM**

**1625**

CFM  
2200 MAX

**3**

SPEED

Featuring three speed choices, the WORKSHOP Air Mover provides high volume air circulation to dry wet carpets, floors, entrances, etc.

- 3 Speed:
  - Hi - 3.0 Amp
  - Med - 2.7 Amp
  - Lo - 2.4 Amp



WORKSHOP kits, hoses and accessories come in 3 diameters:



For maneuverability  
in tight spaces



A great blend of  
maneuverability and  
airflow



Allows for larger sized  
debris collection &  
maximum airflow

## ACCESSORY KITS

Accessory kits conveniently provide a set of tools needed for general and specialized tasks.



**Gutter Cleaning Kit**  
WS25051A



**Premium Auto Cleaning Kit**  
WS12552A



**3 Piece Kit**  
WS17853A  
Wet Nozzle, Crevice Tool, Dusting Brush



**6 Piece Kit**  
WS17856A  
2 Extension Wands, Utility Nozzle,  
Dusting Brush, Wet Nozzle, Crevice Tool



The WORKSHOP 2½" standard hose features Dual-Flex™ technology that resists crimping and collapsing, and adds 180° flexibility at both hose ends for enhanced maneuverability.

**CONTRACTOR**  
**LOCKING HOSE**

The Contractor grade hose is more flexible and durable than a standard hose.



**6' Hose**  
WS12520A



**Expandable Locking Hose**  
Expands from 2'-7'  
WS17821A



**7' Locking Hose**  
Locking tab quickly secures  
WS17820A

**CONTRACTOR**  
**LOCKING HOSE**



**10' Contractor Locking Hose**  
WS17823A



**7' Dual-Flex™ Locking Hose**  
WS25020A

**ACCESSORIES**

Choose the right tool for the job. Pairing the right hand tool, floor tool or wand with your WORKSHOP Wet Dry Vac makes every cleanup job faster and more efficient.

**Utility Nozzle**

Pick-up for large debris  
1¼" / WS12509A  
1⅞" / WS17809A  
2½" / WS25009A

**Wet Nozzle**

Squeegee for liquid clean-up  
1¼" / WS12510A  
1⅞" / WS17810A  
2½" / WS25010A

**Extension Wand**

Extends Reach  
1¼" / WS12508A  
1⅞" / WS17808A  
2½" / WS25008A

**Dusting Brush**

Dusts as it cleans  
1¼" / WS12501A  
1⅞" / WS17801A  
2½" / WS25001A

**Crevice Tool**

Gets into tight spaces  
1¼" / WS12502A  
1⅞" / WS17802A  
2½" / WS25002A

**Car Nozzle**

Deep vehicle cleaning  
1⅞" / WS17803A  
2½" / WS25003A

**Floor Brush**

Large area floor cleaning  
1⅞" / WS17814A  
2½" / WS25014A

**Claw Nozzle**

Deep and thorough cleaning  
1¼", 1⅞", 2½" / WS17840A  
Not for use with WS17821A

**Blower Nozzle**

Concentrated blowing  
2½" / WS25006A

**Diffuser/Muffler**

For quieter operation  
2½" / WS25025A

**Universal Tool Adapter**

Connect power tools to hose  
WS25007A

**2½" - 1¼" Adapter**

Adapts 2½" Hose to  
1¼" Accessories  
WS25011A

## CARTRIDGE FILTERS

WORKSHOP cartridge filters not only protect the vac's internal components from damaging debris, but also prevent harmful contaminants from re-entering the atmosphere. There's a filter to stop all sorts of debris, from everyday dirt to drywall dust to pollens and allergens. There's even a WET ONLY filter for the most demanding, high volume water-borne debris situations.



WS11045F      WS21200F

### STANDARD FILTERS

5 Microns @ 95% Efficiency

#### Best For

- Sawdust
- Typical Basement, Garage, or Car Dirt

Short filters (WS11045F & WS12045F) fit 3 to 4.5 gallon vacs plus WS0500VA.

All other filters fit 5 to 16 gallon vacs, except WS0500VA.



WS12045F      WS22200F

### FINE DUST FILTERS

1 Micron @ 99% Efficiency

#### Best For

- Same as Standard Filter Plus...
- Drywall Dust
- Cement Dust
- Cold Ashes  
Fireplace  
BBQ Grill
- Fine Powders  
Flour  
Talcum/Baby Powder  
Chalk

## DUST COLLECTION BAGS

Dust bags make collection and disposal of dry debris cleaner, easier and more convenient.



WS32045F  
Fits 3-4.5 Gallon Vacs



WS32090F  
Fits 6-9 Gallon Vacs  
plus WS0500VA



WS32200F  
Fits 12-16 Gallon Vacs

#### Best For

- Dry, Everyday Dirt And Fine Particle Debris Like Drywall Dust
- Note: These bags only work and fit vacs with inlets in the collection drum.



**QWIKLOCK™**

PATENTED FILTER FASTENING SYSTEM

Makes installing and removing your filter quick, easy and secure.



WS23200F

**HEPA MEDIA FILTER**

0.3 Microns @ 99.97% Efficiency

**Best For**

- Same as Fine Dust Filter Plus...
- Pet Dander
- Pollens
- Allergens
- Fine Indoor Particles
  - Upholstery
  - Dust Mites
  - Mold Spores
  - Dryer Lint
  - Furnace Filter



WS24200F

**WET ONLY FILTER**

**For**

- High-Volume Liquid
- Water-Borne Debris

The wet filter has a foam outer layer with structural resin core designed to add protection for your vac during high volume liquid pick-up.

**FILTER BAG**



WS01025F

Fits 2.5 Gallon Vacs  
plus WS0500VA

**FILTER MAINTENANCE**

Cleaning or replacing your filter regularly helps minimize motor load and extends the life of your vac. We recommend changing your pleated paper filter at least twice a year.



# WORKSHOP<sup>®</sup>

WET/DRY VACCS

8100 West Florissant

St. Louis, MO 63136

[www.WORKSHOPvaccs.com](http://www.WORKSHOPvaccs.com)

1-888-455-8724



WORKSHOPbrand



FA0 SP6884 0002

[www.WORKSHOPvaccs.com](http://www.WORKSHOPvaccs.com)

