

# WORKSHOP<sup>®</sup> MD

## WET/DRY VACS

6.5

PEAK HP

11

US  
GALLON

### MOBILE VAC STATION

The Mobile Vac Station is the ultimate in organized storage, easy debris disposal, power and convenience.

- Easy To Reach Storage Drawers Keep Hose And Accessories Close At Hand
- Slide-Out Drum For Clean And Easy Filter Changes And Debris Removal
- Qwik Lock<sup>®</sup> Filter Fastening System For Easy Filter Changes
- Ergonomic Handle And Large Rear Wheels Transport Easily Over Rough Terrain And Stairs
- Contractor Grade Locking Hose Offers Maximum Durability And Flexibility
- Flat, Hinged Top Also Doubles As A Secondary Work Surface



1 7/8"

DIAMETER



Includes: Vac, Hose, Utility Nozzle, Crevice Tool, Dusting Brush, Wet Nozzle, Claw Nozzle, 2 Extension Wands, Fine Dust Filter, Owner's Manual

WS1100CA

5 YEAR\*  
LIMITED  
WARRANTY

# WORKSHOP<sup>®</sup> MD

## WET/DRY VACS

www.WORKSHOPvacs.com

6.5

PEAK HP

11

US  
GALLON

### SPECIFICATIONS

Drum Size	11 Gal / 41 L
Peak H.P.	6.5
Voltage	120
Amps	12.0
CFM	127
Static Lift	48 in
Max Air Watts	217
Blowing Capability	Yes
Cord Length	20' / 6 m
Hose Length	10' / 3 m
Drain Port	Yes
Construction	Polypropylene
Accessory Size	1 7/8" / 6,4 cm
Accessory Storage	Yes - Drawers
U.L. Listed	Yes
Fine Dust Filter	WS22200F

20'/6M

Flat, hinged top provides easy access to the hose drawer, and when closed provides a flat working surface.

Hose and accessory storage drawers keep hose and accessories organized and within easy reach.

Large, easy access power switch for quick operation.

Large latches make emptying the drum or changing the filter a snap.

Tough, copolymer drum resists dents and cracks, will not rust.

Large casters and rear wheels provide mobility up steps and over rough terrain.

Large drain located at the drum's lowest point for quick and easy liquid disposal.

Cart handle improves vac mobility and reduces bending and reaching.

Blowing port for added versatility.

Flat drum lid catches debris during filter changes to reduce mess.

Locking rear wheels keep the vac from rolling on inclined surfaces.

Supply caddy keeps extra supplies (not included) on-board and within reach.



Qwik Lock<sup>®</sup> Filter Fastening System –  
Makes installing or removing your filter  
quick, easy and secure.



### CONTRACTOR GRADE LOCKING HOSE

The Contractor grade hose is more flexible  
and durable than a standard hose.



WORKSHOP<sup>®</sup> Wet/Dry Vacs  
8100 West Florissant  
St. Louis, MO 63136

1-888-455-8724



WORKSHOPbrand

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.