

WORKSHOP[®] MD

WET/DRY VACS

5.0

PEAK HP

4

US
GALLON

PORTABLE VAC

The 4 Gallon Portable Vac delivers high performance in a compact package and is convenient to carry, transport and store.

- Powerful Performance In A Lightweight, Portable Design
- Qwik Lock[®] Filter Fastening System For Easy Filter Changes
- Integral Blowing Port For Added Versatility
- Large Handle And Power Switch Improves Usability
- Large Latches Holds Drum Securely In Place
- Locking Hose Won't Pull Out During Use



1 7/8"

DIAMETER



Includes: Vac, Hose, Car Nozzle, Muffler/Diffuser, Standard Filter, Dust Bag, Owner's Manual

WS0400VA

5 YEAR*
LIMITED
WARRANTY

WORKSHOP[®] MD

WET/DRY VACS

www.WORKSHOPvacs.com

5.0

PEAK HP

4

US
GALLON

SPECIFICATIONS

Drum Size	4 Gal / 15 L
Peak H.P.	5.0
Voltage	120
Amps	9.0
CFM	109
Static Lift	47 in
Max Air Watts	177
Blowing Capability	Yes
Cord Length	20' / 6,1 m
Hose Length	7' / 2,1 m
Drain Port	No
Construction	Polypropylene
Accessory Size	1 7/8" / 4,8 cm
Accessory Storage	Yes - In Handle
U.L. Listed	Yes
Standard Filter	WS11045F
Dust Collection Bag	WS32045F

OPTIONAL FILTRATION

Fine Dust Filter	WS12045F
------------------	----------



Qwik Lock[®] Filter Fastening System –
Makes installing or removing your filter
quick, easy and secure.



20' / 6M

Large carrying handle with built in storage keeps car nozzle close at hand and transports easily.

Convenient cord wrap.

Ergonomic power switch allows user to easily carry and turn vac On/Off with the same hand.

Blowing port for added versatility.

1 7/8" x 7' Quick-release locking hose stays secure during use.

Easy open large latches provide secure drum fit.

Tough, copolymer drum resists dents and cracks, will not rust.

Compact size is lightweight and portable.



WORKSHOP[®] Wet/Dry Vacs
8100 West Florissant
St. Louis, MO 63136

1-888-455-8724



Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.