

# WORKSHOP<sup>®</sup> MD

## WET/DRY VACS

2.5

PEAK HP

4

US  
GALLON

- **Stainless Steel Drum Cleans Up Easily For A Professional Appearance**
- **On-Board Storage Keeps Accessories Secure And Within Close Reach**
- **Integral Blowing Port For Added Versatility**
- **Quick-Release Locking Hose Stays Secure During Use**

### STAINLESS STEEL PORTABLE VAC

The 4 Gallon Stainless Steel Vac is compact and easy to carry, transport and store.



1 7/8"

DIAMETER



Includes: Vac, Hose, Utility Nozzle, Wet Nozzle, 2 Extension Wands, Filter Bag, Owner's Manual

WS0400SS

5 YEAR\*  
LIMITED  
WARRANTY

# WORKSHOP<sup>®</sup> MD

## WET/DRY VACS

www.WORKSHOPvacs.com

2.5


PEAK HP

4

US  
GALLON

### SPECIFICATIONS

Drum Size	4 Gal / 15 L
Peak H.P.	2.5
Voltage	120
Amps	5.8
CFM	61
Static Lift	58 in
Max Air Watts	141.7
Blowing Capability	Yes
Cord Length	10' / 3 m
Hose Length	7' / 2,1 m
Drain Port	No
Construction	Stainless Steel
Accessory Size	1 7/8" / 4,8 cm
Accessory Storage	Yes - Caster Feet
U.L. Listed	Yes
Filter Bag	WS01025F



Large carrying handle provides easy transport.

Convenient cord wrap.

1 7/8" x 7' Quick-release locking hose stays secure during use.

On-board accessory storage keeps included accessories close at hand.

Easy open latches provide secure drum fit.

Stainless steel drum provides high quality, rugged construction.



### OPTIONAL FILTRATION

Standard Filter	WS11045F
Fine Dust Filter	WS12045F



WORKSHOP<sup>®</sup> Wet/Dry Vacs  
8100 West Florissant  
St. Louis, MO 63136

1-888-455-8724



WORKSHOPbrand

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.