WORKSHOP®MD

WET/DRY VACS

1.75 PEAK HP

2.5 US GALLON

- Compact Design Is Lightweight And Portable
- On-Board Storage Keeps Hose And Accessories Secure And Within Reach
- Compact Design Is Ideal For Around The House And Conveniently Stores In Most Cabinets Or Pantries
- Handle Doubles As A Cord-Wrap
- Hold And Turn On/Off With The Same Hand
- Integral Blowing Port For Added Versatility

COMPACT VAC

This compact, lightweight vac is so easy to carry and store, and really handy for quick pick-ups around the house.



1¼" DIAMETER







Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Filter Bag, Owner's Manual

WS0255VA

5 YEAR* LIMITED WARRANTY

WORKSHOP®MD

WET/DRY VACS

1.75 PEAK HP


2.5 US GALLON

SPECIFICATIONS

Drum Size	2.5 Gal / 9.5 L
Peak H.P.	1.75
Voltage	120
Amps	4.0
CFM	49
Static Lift	31 in
Max Air Watts	54
Blowing Capability	Yes
Cord Length	10' / 3 m
Hose Length	4' / 1,2 m
Drain Port	No
Construction	Polypropylene
Accessory Size	1¼" / 3,1 cm
Accessory Storage	Yes - Caddy
U.L. Listed	Yes
Filter Bag	WS01025F

10'/3M





Replacement Filter Bag – Easy to install replacement filter WS01025F.





c UL us LISTED

Emerson Tool Company
12969 Manchester Road
St. Louis, MO 63131

1-888-455-8724

WORKSHOPbrand

YouTube

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.

WORKSHOP® WET/DRY VACS

3.5 PEAK HP

3 US GALLON

- Specialized Tools Perfect For Auto Cleaning And Detailing
- The Ideal Auto Cleaning Vacuum
- Compact Design Is Powerful, Lightweight And Portable
- Qwik Lock® Filter Fastening System For Easy Filter Changes
- Locking Hose Expands From 2'-7' For Extended Reach And Convenient Storage
- Built-in Suction Powered Dust Pan Makes Cleanup Quick & Easy
- Quick-Release Cord Wrap Stores Power Cord On-Board

PORTABLE VAC

With it's unique built-in dust pan feature and un matched portability, the 3 gallon is the ideal vac for auto, job site and workbench cleaning.

IDEAL FOR AUTO DETAILING



1 7/8" DIAMETER







Includes: Vac, Hose, Car Nozzle, Flexible Crevice Tool, Claw Nozzle, Dusting Brush, Standard Filter, Dust Bag, Owner's Manual

WS0301VA

5 YEAR* LIMITED WARRANTY

WORKSHOP® MD
WET/DRY VACS

3.5 PEAK HP

3 US GALLON

SPECIFICATIONS

Drum Size	3 Gal / 11 L
Peak H.P.	3.5
Voltage	120
Amps	7.0
CFM	60
Static Lift	64 in
Max Air Watts	164
Blowing Capability	No
Cord Length	10' / 3 m
Hose Length	2'-7' / 2,1 m
Drain Port	No
Construction	Polypropylene
Accessory Size	1⅞" / 4,8 cm
Accessory Storage	Yes - Handle Clips
U.L. Listed	Yes
Standard Filter	WS11045F
Dust Collection Bag	WS32045F

OPTIONAL FILTRATION

Standard Filter	WS11045F
HEPA Media Filter	WS13045F
Wet Application Filter	WS14045F

QWIK LOCK® MD

Qwik Lock® Filter Fastening System – Makes installing or removing your filter quick, easy and secure.

c UL us LISTED

10'/3M



Large carrying handle with built in hose storage transports vac easily.

Compact size is lightweight and portable.

Convenient cord wrap with quick-release.

Easy access power switch for quick operation.

Large latches provide secure drum fit.

1⅞" Expandable locking hose stretches from 2'-7' for extended reach and convenient storage. Bleeder valve allows control of suction.

Suction powered dust pan makes cleaning fast and easy.

Tough, copolymer drum resists dents and cracks, will not rust.





Emerson Tool Company
12969 Manchester Road
St. Louis, MO 63131

1-888-455-8724

WORKSHOPbrand

You Tube

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.

WORKSHOP® WET/DRY VACS

6.0 PEAK HP

4 US GALLON

- Power Head Detaches To Become A High Performance Hand-Held Blower
- Powerful Performance In A Lightweight, Portable Design
- Qwik Lock® Filter Fastening System For Easy Filter Changes
- Large Handle And Power Switch Improves Usability
- Large Latches Holds Drum Securely In Place
- Locking Hose Won't Pull Out During Use

DETACHABLE BLOWER VAC

The 4 Gallon Detachable Blower Vac delivers high performance in a compact package and is convenient to carry, transport and store.



1 7/8" DIAMETER







Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Blower Wand, 2 Extension Wands, Filter, Dust Bag, Owner's Manual

WS0400DE

5 YEAR* LIMITED WARRANTY

WORKSHOP® MD

WET/DRY VACS

6.0 PEAK HP

4 US GALLON

SPECIFICATIONS

Drum Size	4 Gal / 15 L
Peak H.P.	6.0
Voltage	120
Amps	10.0
CFM	125
Static Lift	52 in
Max Air Watts	234
Blowing Capability	Yes - Detachable
Cord Length	20' / 6,1 m
Hose Length	7' / 2,1 m
Drain Port	No
Construction	Polypropylene
Accessory Size	1⅞" / 4,8 cm
Accessory Storage	Yes - Rear Caddy
U.L. Listed	Yes
Fine Dust Filter	WS12045F
Dust Collection Bag	WS32045F

OPTIONAL FILTRATION

Standard Filter	WS11045F
HEPA Media Filter	WS13045F
Wet Application Filter	WS14045F

QWIK LOCK® MD

Qwik Lock® Filter Fastening System – Makes installing or removing your filter quick, easy and secure.

c UL us LISTED

20'/6M



High performance vacuum power head doubles as a detachable leaf blower for added convenience and versatility.

Convenient cord wrap.

Ergonomic power switch allows user to easily carry and turn vac On/Off with the same hand.

Storage caddy keeps wands and accessory nozzles close at hand.

1⅞" x 7' Quick-release locking hose stays secure during use.

Tough, copolymer drum resists dents and cracks, will not rust.

Easy open large latches provide secure drum fit.





Emerson Tool Company
12969 Manchester Road
St. Louis, MO 63131

1-888-455-8724

WORKSHOPbrand

You Tube

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.

WORKSHOP® WET/DRY VACS

5.0 PEAK HP

5 US GALLON

- Specialized Tools Perfect For Auto Cleaning And Detailing
- Save Valuable Floor Space And Stay Organized With This Portable/Wall Mounted System
- 2'-7' Expandable Hose Plus 14' Of Additional Hose Provides 21' Of Reach
- Qwik Lock® Filter Fastening System For Easy Filter Changes
- On-Board Storage Keeps Hose And Accessories Conveniently Accessible And Ready To Go
- Large Latches Holds Drum Securely In Place

PORTABLE / WALL MOUNT VAC

Mount it to the wall or take it with you, this vac helps save floor space while providing all the power and reach you need.

IDEAL FOR AUTO DETAILING



1 7/8" DIAMETER







Includes: Vac, 2 Hoses, Flexible Crevice Tool, Claw Nozzle, Dusting Brush, 2 Extension Wands, Muffler, Standard Filter, Dust Bag, Owner's Manual

WS0501WM

5 YEAR* LIMITED WARRANTY

WORKSHOP®MD

WET/DRY VACS

5.0 PEAK HP

5 US GALLON

SPECIFICATIONS

Drum Size	5 Gal / 19 L
Peak H.P.	5.0
Voltage	120
Amps	8.5
CFM	96
Static Lift	45 in
Max Air Watts	147
Blowing Capability	Yes - Blowing port
Cord Length	20' / 6,1 m
Hose Length	2'-7' / 0,6-2,1 m 14' / 4,2 m
Drain Port	No
Construction	Polypropylene
Accessory Size	1⅞" / 4,8 cm
Accessory Storage	Yes - Bin
U.L. Listed	Yes
Standard Filter	WS21200F
Dust Collection Bag	WS32090F

OPTIONAL FILTRATION

Fine Dust Filter	WS22200F
HEPA Media Filter	WS23200F
Wet Application Filter	WS24200F

QWIKLOCK®MD

Qwik Lock® Filter Fastening System – Makes installing or removing your filter quick, easy and secure.

c UL US LISTED

20'/6M

Cord wrap on back of vac.

Easy to install bracket mounts vac to the wall. Use while attached or release to carry vac with you as needed.

Hose storage keeps both hoses neatly stored when not in use.

Top carrying handle provides easy transport.

Easy access power switch for quick operation.



Blowing port for added versatility.

Two Hoses Included –
- 1⅞" Locking Hose – Length expands from 2'-7'.
- 1⅞" x 14' Locking Hose – Won't pull out of vac until released.

On-board accessory storage bin keeps accessories close at hand.

Tough, copolymer drum resists dents and cracks, will not rust.





Emerson Tool Company
12969 Manchester Road
St. Louis, MO 63131

1-888-455-8724

WORKSHOPbrand

YouTube

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.

WORKSHOP® WET/DRY VACS

4.25 PEAK HP

9 US GALLON

GENERAL PURPOSE VAC

Stepping up in power and drum capacity, the 9 Gallon Vac remains easy to maneuver and store.

- On-Board Storage Keeps Accessories Secure And Within Close Reach
- Qwik Lock® Filter Fastening System For Easy Filter Changes
- Integral Blowing Port For Added Versatility
- Quick-Release Locking Hose Stays Secure During Use
- Large Carry Handle For Easy Transport



1 7/8" DIAMETER







Includes: Vac, Hose, Utility Nozzle, Wet Nozzle, Car Nozzle, 2 Extension Wands, Standard Filter, Dust Bag, Owner's Manual

WS0915VA

5 YEAR* LIMITED WARRANTY

WORKSHOP®MD
WET/DRY VACS

4.25 PEAK HP

9 US GALLON

SPECIFICATIONS

Drum Size	9 Gal / 34 L
Peak H.P.	4.25
Voltage	120
Amps	8.3
CFM	69
Static Lift	71 in
Max Air Watts	209
Blowing Capability	Yes
Cord Length	10' / 3 m
Hose Length	7' / 2,1 m
Drain Port	No
Construction	Polypropylene
Accessory Size	1⅞" / 4,8 cm
Accessory Storage	Yes - Caster Feet
U.L. Listed	Yes
Standard Filter	WS21200F
Dust Collection Bag	WS32090F

OPTIONAL FILTRATION

Fine Dust Filter	WS22200F
HEPA Media Filter	WS23200F
Wet Application Filter	WS24200F

QWIK LOCK®MD

Qwik Lock® Filter Fastening System – Makes installing or removing your filter quick, easy and secure.

c UL US LISTED

10'/3M







Emerson Tool Company
12969 Manchester Road
St. Louis, MO 63131

1-888-455-8724

WORKSHOPbrand

YouTube

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.

WORKSHOP® WET/DRY VACS

5.0 PEAK HP

12 US GALLON

- On-Board Storage Keeps Hose And Accessories Secure And Within Reach
- Qwik Lock® Filter Fastening System For Easy Filter Changes
- Dual-Flex® Locking Hose Offers 180° Flexibility At Both Hose Ends For Better Maneuverability
- Large Drain For Easier Liquid Disposal
- Large Carry Handle For Easy Transport
- Integral Blowing Port For Added Versatility

HIGH-POWER GENERAL PURPOSE VAC

Equally at home on the job or in the shop, the 12 Gallon General Purpose Vac delivers the ideal combination of performance, drum capacity and convenience.



2½" DIAMETER







Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Wet Nozzle, 2 Extension Wands, Filter, Dust Bag, Owner's Manual

WS1200VA

5 YEAR* LIMITED WARRANTY

WORKSHOP®MD

WET/DRY VACS

5.0 PEAK HP

12 US GALLON

SPECIFICATIONS

Drum Size	12 Gal / 45 L
Peak H.P.	5.0
Voltage	120
Amps	10.0
CFM	135
Static Lift	47 in
Max Air Watts	209
Blowing Capability	Yes
Cord Length	15' / 4,5 m
Hose Length	7' / 2,1 m
Drain Port	Yes
Construction	Polypropylene
Accessory Size	2½" / 6,4 cm
Accessory Storage	Yes - Caster Feet
U.L. Listed	Yes
Standard Filter	WS21200F
Dust Collection Bag	WS32200F

OPTIONAL FILTRATION

Fine Dust Filter	WS22200F
HEPA Media Filter	WS23200F
Wet Application Filter	WS24200F

QWIK LOCK®MD

Qwik Lock® Filter Fastening System – Makes installing or removing your filter quick, easy and secure.

c UL us LISTED

15'/4,5M







Emerson Tool Company
12969 Manchester Road
St. Louis, MO 63131

1-888-455-8724

WORKSHOPbrand

YouTube

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.

WORKSHOP® WET/DRY VACS

6.0 PEAK HP

14 US GALLON

- Ergonomic Handle And Large Rear Wheels Transport Easily Over Rough Terrain And Stairs
- Qwik Lock® Filter Fastening System For Easy Filter Changes
- Easy To Reach Storage Bag Keeps Accessories Close At Hand
- Hose Stores Conveniently On-Board
- Integral Blowing Port For Added Versatility
- Cart System Reduces Bending And Reaching Making Your Work Quicker And Easier
- One Of The Quietest Vacs In The WORKSHOP Line

HIGH-POWER CART VAC

Rough terrain mobility, reduced noise, high performance and rugged 2-piece drum construction are this vac's hallmarks.



2½" DIAMETER







Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Wet Nozzle, 2 Extension Wands, Fine Dust Filter, Dust Bag, Owner's Manual

WS1400CA

5 YEAR* LIMITED WARRANTY

WORKSHOP® MD
WET/DRY VACS

6.0 PEAK HP

14 US GALLON

SPECIFICATIONS

Drum Size	14 Gal / 52 L
Peak H.P.	6.0
Voltage	120
Amps	11.0
CFM	143
Static Lift	47 in
Max Air Watts	217
Blowing Capability	Yes
Cord Length	20' / 6 m
Hose Length	7' / 2,1 m
Drain Port	Yes
Construction	Polypropylene
Accessory Size	2½" / 6,4 cm
Accessory Storage	Yes - Bag
U.L. Listed	Yes
Fine Dust Filter	WS22200F
Dust Collection Bag	WS32200F

OPTIONAL FILTRATION

Standard Filter	WS21200F
HEPA Media Filter	WS23200F
Wet Application Filter	WS24200F

QWIK LOCK® MD

Qwik Lock® Filter Fastening System – Makes installing or removing your filter quick, easy and secure.

c UL us LISTED

20'/6M

Large carrying handle provides easy transport.

Easy-reach accessory storage bag keeps accessories close at hand.

Convenient cord wrap.

Cart handle with accessory storage improves vac mobility.

Easy access power switch for quick operation.

Blowing port for added versatility.

dual-flex® LOCKING HOSE

2½" x 7' Dual-Flex® Locking Hose offers 180° flexibility at both hose ends for better maneuverability.

Large latches make emptying the drum or changing the filter a snap.

2-piece drum provides rugged construction and increases stability.

Large rear wheels provide mobility up steps, over thresholds, and rough terrain.

Large drain located at the drum's lowest point for quick and easy liquid disposal.





Emerson Tool Company
12969 Manchester Road
St. Louis, MO 63131

1-888-455-8724

WORKSHOPbrand YouTube

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.

WORKSHOP®MD

WET/DRY VACS

6.5 PEAK HP

16 US GALLON

- Stainless Steel Drum Construction Cleans Up Easily For A Professional Appearance
- Qwik Lock® Filter Fastening System For Easy Filter Changes
- Ergonomic Handle And Large Rear Wheels Transport Easily Over Rough Terrain And Stairs
- Easy To Reach Storage Bag Keeps Accessories Close At Hand
- Dual-Flex® Locking Hose Offers 180° Flexibility At Both Hose Ends For Better Maneuverability
- Integral Blowing Port For Added Versatility

STAINLESS STEEL CART VAC

Featuring a Stainless Steel drum and rough terrain cart, this vac out performs under the toughest of conditions.



2½" DIAMETER







Includes: Vac, Hose, Utility Nozzle, Crevice Tool, Car Nozzle, Wet Nozzle, 2 Extension Wands, Fine Dust Filter, Dust Bag, Owner's Manual

WSI600SS

5 YEAR* LIMITED WARRANTY

WORKSHOP® MD
WET/DRY VACS

6.5 PEAK HP

16 US GALLON

SPECIFICATIONS

Drum Size	16 Gal / 60 L
Peak H.P.	6.5
Voltage	120
Amps	12.0
CFM	181
Static Lift	45 in
Max Air Watts	280
Blowing Capability	Yes
Cord Length	20' / 3 m
Hose Length	7' / 2,1 m
Drain Port	Yes
Construction	Polypropylene
Accessory Size	2½" / 6,4 cm
Accessory Storage	Yes - Bag
U.L. Listed	Yes
Fine Dust Filter	WS22200F
Dust Collection Bag	WS32200F

OPTIONAL FILTRATION

Standard Filter	WS21200F
HEPA Media Filter	WS23200F
Wet Application Filter	WS24200F

QWIK LOCK® MD

Qwik Lock® Filter Fastening System – Makes installing or removing your filter quick, easy and secure.

c UL us LISTED

20'/6M

Large carrying handle provides easy transport.

Easy reach accessory storage keeps accessories close at hand.

Convenient cord wrap.

Easy access power switch for quick operation.

Cart handle with accessory storage improves vac mobility.

Blowing port for added versatility.

dual-flex® LOCKING HOSE

2½" x 7' Dual-Flex® Locking Hose offers 180° flexibility at both hose ends for better maneuverability.

Large rear wheels provide mobility up steps, over thresholds, and rough terrain.

Stainless steel drum – high quality, rugged construction.

Large drain located at the drum's lowest point for quick and easy liquid disposal.





Emerson Tool Company
12969 Manchester Road
St. Louis, MO 63131

1-888-455-8724

WORKSHOPbrand YouTube

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.

WORKSHOP® WET/DRY VACS

6.5 PEAK HP

16 US GALLON

- Largest Drum Size And Most Power In The Line
- Dual-Flex® Locking Hose Offers 180° Flexibility At Both Hose Ends For Better Maneuverability
- Qwik Lock® Filter Fastening System For Easy Filter Changes
- On-Board Storage Keeps Accessories Secure And Within Reach
- Integral Blowing Port For Added Versatility

HIGH-CAPACITY VAC

This no nonsense 16 Gallon Vac has the power, durability and collection capacity to be the job site workhorse.



2½" DIAMETER







Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Wet Nozzle, 2 Extension Wands, Standard Filter, Owner's Manual

WS1600VA

5 YEAR* LIMITED WARRANTY

WORKSHOP® MD
WET/DRY VACS

6.5 PEAK HP

16 US GALLON

SPECIFICATIONS

Drum Size	16 Gal / 60 L
Peak H.P.	6.5
Voltage	120
Amps	12.0
CFM	169
Static Lift	46 in
Max Air Watts	265
Blowing Capability	Yes
Cord Length	20' / 6 m
Hose Length	7' / 2,1 m
Drain Port	Yes
Construction	Polypropylene
Accessory Size	2½" / 6,4 cm
Accessory Storage	Yes - Caster Feet & Lid
U.L. Listed	Yes
Standard Filter	WS21200F

OPTIONAL FILTRATION

Fine Dust Filter	WS22200F
HEPA Media Filter	WS23200F
Wet Application Filter	WS24200F

QWIK LOCK® MD

Qwik Lock® Filter Fastening System – Makes installing or removing your filter quick, easy and secure.

c UL US LISTED

20'/6M

Large carrying handle provides easy transport.

Blowing port for added versatility.

Easy-reach accessory storage on the lid keeps accessories secure and easy to reach.

dual-flex® LOCKING HOSE

2½" x 7' Dual-Flex® Locking Hose offers 180° flexibility at both hose ends for better maneuverability.



Large latches make emptying the drum or changing the filter a snap.

Tough, copolymer drum resists dents and cracks, will not rust.

Additional accessory storage on caster feet.

Large drain located at the drum's lowest point for quick and easy liquid disposal.





Emerson Tool Company
12969 Manchester Road
St. Louis, MO 63131

1-888-455-8724

WORKSHOPbrand

YouTube

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.