

WORKSHOP[®] MD

WET/DRY VACS

3.5
PEAK HP

3
US
GALLON

- Specialized Tools Perfect For Auto Cleaning And Detailing
- The Ideal Auto Cleaning Vacuum
- Compact Design Is Powerful, Lightweight And Portable
- Qwik Lock[®] Filter Fastening System For Easy Filter Changes
- Locking Hose Expands From 2'-7' For Extended Reach And Convenient Storage
- Built-in Suction Powered Dust Pan Makes Cleanup Quick & Easy
- Quick-Release Cord Wrap Stores Power Cord On-Board

PORTABLE VAC

With it's unique built-in dust pan feature and un matched portability, the 3 gallon is the ideal vac for auto, job site and workbench cleaning.

**IDEAL FOR
AUTO DETAILING**



1 7/8"
DIAMETER



Includes: Vac, Hose, Car Nozzle, Flexible Crevice Tool, Claw Nozzle, Dusting Brush, Standard Filter, Dust Bag, Owner's Manual

WS030IVA

5 YEAR*
LIMITED
WARRANTY

WORKSHOP[®] MD

WET/DRY VACS

www.WORKSHOPvacs.com

3.5

PEAK HP

3

US
GALLON

SPECIFICATIONS

Drum Size	3 Gal / 11 L
Peak H.P.	3.5
Voltage	120
Amps	7.0
CFM	60
Static Lift	64 in
Max Air Watts	164
Blowing Capability	No
Cord Length	10' / 3 m
Hose Length	2'-7' / 2,1 m
Drain Port	No
Construction	Polypropylene
Accessory Size	1 7/8" / 4,8 cm
Accessory Storage	Yes - Handle Clips
U.L. Listed	Yes
Standard Filter	WS11045F
Dust Collection Bag	WS32045F

OPTIONAL FILTRATION

Fine Dust Filter	WS12045F
------------------	----------



Qwik Lock[®] Filter Fastening System –
Makes installing or removing your filter
quick, easy and secure.



10'/3M

Large carrying handle with built in hose storage transports vac easily.

Compact size is lightweight and portable.

Convenient cord wrap with quick-release.

Easy access power switch for quick operation.

Large latches provide secure drum fit.

Suction powered dust pan makes cleaning fast and easy.

Tough, copolymer drum resists dents and cracks, will not rust.

1 7/8" Expandable locking hose stretches from 2'-7' for extended reach and convenient storage. Bleeder valve allows control of suction.



WORKSHOP[®] Wet/Dry Vacs
8100 West Florissant
St. Louis, MO 63136

1-888-455-8724

WORKSHOPbrand



Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.