

WORKSHOP[®] MD

WET/DRY VACS

6.0

PEAK HP

14

US
GALLON

- Ergonomic Handle And Large Rear Wheels Transport Easily Over Rough Terrain And Stairs
- Qwik Lock[®] Filter Fastening System For Easy Filter Changes
- Easy To Reach Storage Bag Keeps Accessories Close At Hand
- Hose Stores Conveniently On-Board
- Integral Blowing Port For Added Versatility
- Cart System Reduces Bending And Reaching Making Your Work Quicker And Easier
- One Of The Quietest Vacs In The WORKSHOP Line

HIGH-POWER CART VAC

Rough terrain mobility, reduced noise, high performance and rugged 2-piece drum construction are this vac's hallmarks.



2 1/2"

DIAMETER



Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Wet Nozzle, 2 Extension Wands, Locking Sleeve, Fine Dust Filter, Dust Bag, Owner's Manual

WSI400CA

5 YEAR*
LIMITED
WARRANTY

WORKSHOP[®] MD

WET/DRY VACS

www.WORKSHOPvacs.com

6.0

PEAK HP

14

US
GALLON

SPECIFICATIONS

Drum Size	14 Gal /52 L
Peak H.P.	6.0
Voltage	120
Amps	11.0
CFM	143
Static Lift	47 in
Max Air Watts	217
Blowing Capability	Yes
Cord Length	20' / 6 m
Hose Length	7' / 2,1 m
Drain Port	Yes
Construction	Polypropylene
Accessory Size	2½" / 6,4 cm
Accessory Storage	Yes - Bag
U.L. Listed	Yes
Standard Filter	WS21200F
Dust Collection Bag	WS32200F

20'/6M

Large carrying handle provides easy transport.

Easy-reach accessory storage bag keeps accessories close at hand.

Convenient cord wrap.

Easy access power switch for quick operation.

Cart handle with accessory storage improves vac mobility.



2½" x 7' Dual-Flex[®] Locking Hose offers 180° flexibility at both hose ends for better maneuverability.

Blowing port for added versatility.

Large latches make emptying the drum or changing the filter a snap.

2-piece drum provides rugged construction and increases stability.



Large drain located at the drum's lowest point for quick and easy liquid disposal.

Large rear wheels provide mobility up steps, over thresholds, and rough terrain.

OPTIONAL FILTRATION

Fine Dust Filter	WS22200F
HEPA Media Filter	WS23200F
Wet Application Filter	WS24200F



Qwik Lock[®] Filter Fastening System – Makes installing or removing your filter quick, easy and secure.



Keeps accessories securely connected.



WORKSHOP[®] Wet/Dry Vacs
8100 West Florissant
St. Louis, MO 63136

1-888-455-8724



WORKSHOPbrand

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.