

# WORKSHOP<sup>®</sup> MD

## WET/DRY VACS

6.5

PEAK HP

16

US  
GALLON

### HIGH-CAPACITY VAC

This no nonsense 16 Gallon Vac has the power, durability and collection capacity to be the job site workhorse.

- Largest Drum Size And Most Power In The Line
- Dual-Flex<sup>®</sup> Locking Hose Offers 180° Flexibility At Both Hose Ends For Better Maneuverability
- Qwik Lock<sup>®</sup> Filter Fastening System For Easy Filter Changes
- On-Board Storage Keeps Accessories Secure And Within Reach
- Integral Blowing Port For Added Versatility



2 1/2"

DIAMETER



Includes: Vac, Hose, Utility Nozzle, Car Nozzle, Wet Nozzle, 2 Extension Wands, Locking Sleeve, Standard Filter, Owner's Manual

WSI600VA

5 YEAR\*  
LIMITED  
WARRANTY

# WORKSHOP<sup>®</sup> MD

## WET/DRY VACS

www.WORKSHOPvacs.com

**6.5**

PEAK HP

**16**

US GALLON

### SPECIFICATIONS

Drum Size	16 Gal / 60 L
Peak H.P.	6.5
Voltage	120
Amps	12.0
CFM	169
Static Lift	46 in
Max Air Watts	265
Blowing Capability	Yes
Cord Length	20' / 6 m
Hose Length	7' / 2,1 m
Drain Port	Yes
Construction	Polypropylene
Accessory Size	2½" / 6,4 cm
Accessory Storage	Yes - Caster Feet & Lid
U.L. Listed	Yes
Standard Filter	WS21200F

**20'/6M**

Large carrying handle provides easy transport.

Blowing port for added versatility.

Easy-reach accessory storage on the lid keeps accessories secure and easy to reach.



2½" x 7' Dual-Flex<sup>®</sup> Locking Hose offers 180° flexibility at both hose ends for better maneuverability.

Large latches make emptying the drum or changing the filter a snap.

Tough, copolymer drum resists dents and cracks, will not rust.



Additional accessory storage on caster feet.

Large drain located at the drum's lowest point for quick and easy liquid disposal.

### OPTIONAL FILTRATION

Fine Dust Filter	WS22200F
HEPA Media Filter	WS23200F
Wet Application Filter	WS24200F



Qwik Lock<sup>®</sup> Filter Fastening System – Makes installing or removing your filter quick, easy and secure.



WORKSHOP<sup>®</sup> Wet/Dry Vacs  
8100 West Florissant  
St. Louis, MO 63136

1-888-455-8724



WORKSHOPbrand

Real-world performance data achieved from testing at the end of the hose. Competitors typically test at or near motor. Gallons indicated reflect drum volume, not necessarily collection capacity. Actual capacity dependent upon type of debris collected, condition of filter, and other factors. Peak Horsepower represents a level at or below the maximum horsepower output of an electric motor tested in a laboratory using a dynamometer. All details subject to change without notice.